



# International Filter Products

*Revolutionary systems for your industry*

## C-Flex® 082 TPE Tubing

C-Flex® is the original patented thermoplastic elastomer (TPE) tubing specifically designed to meet the critical demands of pharmaceutical and biopharmaceutical applications for fluid processing with an excellent heat seal and sterile weld capabilities. For over 30 years, C-Flex® has been the thermoplastic elastomer (TPE) tubing most widely used and validated by the world's leading pharmaceutical and biopharmaceutical companies. Each coil of C-Flex® tubing is extruded to precise ID and wall dimensions. C-Flex® 082 is translucent tubing for fluid flow visibility, offering the widest range of formulations and sizes in the industry. C-Flex® tubing has a secure global supply chain with redundant manufacturing sites in the United States and Europe with validated manufacturing processes.



C-Flex® comes in a wide variety of sizes and formulations.



One-piece overmolded C-Flex® manifold maintains inner bore diameters with superior reliability and product integrity.





# International Filter Products

*Revolutionary systems for your industry*

## Application

- Aseptic Sealing Disconnections
- Aseptic Welding Connections
- Ideal For Use in Single-Use Assemblies
- Peristaltic Pump
- Cell Culture Operations
- Acid & Base
- Tubing and Bags Manifolds
- Single-Use Fluid Transfer Sets
- Buffer and Media Preparation

## Technical Data Sheet

### Features and Benefits:

- ❖ Sealable and weldable either pre-or post-sterilization.
- ❖ Sterilizable by gamma irradiation and autoclave.
- ❖ Moldable, bondable, and formable for single-use assemblies and over molds.
- ❖ Temperature range -67°C to 135°C (-85°F to 275°F).
- ❖ Significantly less permeable than silicone.
- ❖ All formulas are Animal-Derived Component Free.
- ❖ All-inclusive Validation Guide and the Regulatory Information Overview (RIO) are available for customers upon request.

### Chemical Resistance:

Chemical Type	C-Flex Compatibility
Acids, Dilute/Weak	Excellent
Acids, Strong/Concentrated	Excellent
Bases, Dilute/Weak	Excellent
Bases, Strong/Concentrated	Excellent
Salts	Excellent
High-purity Water	Excellent

Note: A comprehensive chemical compatibility chart is available upon request.





# International Filter Products

*Revolutionary systems for your industry*

When some chemical types are not suitable, safe, or chemically compatible with C-Flex, Saint-Gobain offers alternative tubing series. Below, you will find chemicals that are incompatible with C-Flex and the suggested alternative Saint-Gobain tubing series:

Chemical Type	Alternative Saint-Gobain Tubing Series
Alcohol	<ul style="list-style-type: none"> <li>i. Sani-Tech</li> <li>ii. PharmaPure</li> <li>iii. PharMed BPT</li> <li>iv. PharmaFluor FEP</li> </ul>
Oil / Water Emulsion	<ul style="list-style-type: none"> <li>i. Sani-Tech</li> <li>ii. PharmaFluor FEP</li> </ul>
Low Spallation Peristaltic Pump Tubing	<ul style="list-style-type: none"> <li>i. PharmaPure</li> </ul>
Biocompatible Peristaltic Pump Tubing	<ul style="list-style-type: none"> <li>i. PharMed BPT</li> </ul>
Ketones and Organic Solvent	<ul style="list-style-type: none"> <li>i. PharmaFluor FEP</li> </ul>

## Physical Properties:

Property	ASTM Method	Formulations Value
Appearance	-	Translucent
Durometer, Shore A	D2240	60
Tensile Strength, psi	D412	1106
Elongation, %	D412	874
Tensile Modulus, @100%/300%, psi	D412	256/400
Tensile Set @ 300% Stretch	D412	29
Compression Set Constant Deflection "B" (22hrs @ 70°C), %	D395	89
Brittle Point, °C	D746	-67









# International Filter Products

*Revolutionary systems for your industry*

## C-Flex 082 Tubing Standard Size:

C-Flex® - 082 - Translucent Tubing Standard Size						
Part Numbers	Standard Coil Length, ft (m)	ID x OD x Wall (inch)	ID x OD x Wall (inch fractions)	ID x OD x Wall (millimeters)	Average Working Pressure (psi): 66°F (19°C)	
					C-Flex® 082	
					psi	bar
082-031-1	50' (15 m)	0.031 x 0.094 x 0.031	1/32 x 3/32 x 1/32	0.8 x 2.4 x 0.8	30	2.1
082-063-1	50' (15 m)	0.063 x 0.125 x 0.031	1/16 x 1/8 x 1/32	1.6 x 3.2 x 0.8	21	1.4
082-063-2	50' (15 m)	0.063 x 0.188 x 0.062	1/16 x 3/16 x 1/16	1.6 x 4.8 x 1.6	46	3.2
082-125-2	50' (15 m)	0.125 x 0.250 x 0.062	1/8 x 1/4 x 1/16	3.2 x 6.4 x 1.6	27	1.9
082-188-2	50' (15 m)	0.188 x 0.313 x 0.062	3/16 x 5/16 x 1/16	4.8 x 8.0 x 1.6	22	1.5
082-188-3	50' (15 m)	0.188 x 0.375 x 0.094	3/16 x 3/8 x 3/32	4.8 x 9.5 x 2.4	36	2.5
082-250-2	50' (15 m)	0.250 x 0.375 x 0.062	1/4 x 3/8 x 1/16	6.4 x 9.5 x 1.6	17	1.2
082-250-3	50' (15 m)	0.250 x 0.438 x 0.094	1/4 x 4/9 x 3/32	6.4 x 11.2 x 2.4	23	1.6
082-250-4	50' (15 m)	0.250 x 0.500 x 0.125	1/4 x 1/2 x 1/8	6.4 x 12.7 x 3.2	30	2
082-313-3	50' (15 m)	0.313 x 0.500 x 0.094	5/16 x 1/2 x 3/32	7.9 x 12.7 x 2.4	20	1.4
082-375-2	50' (15 m)	0.375 x 0.500 x 0.062	3/8 x 1/2 x 1/16	9.6 x 12.7 x 1.6	12	0.8
082-375-3	50' (15 m)	0.375 x 0.563 x 0.094	3/8 x 5/9 x 3/32	9.6 x 14.3 x 2.4	16	1.1
082-375-4	50' (15 m)	0.375 x 0.625 x 0.125	3/8 x 5/8 x 1/8	9.6 x 15.9 x 3.2	21	1.4
082-500-3	50' (15 m)	0.500 x 0.688 x 0.094	1/2 x 2/3 x 3/32	12.7 x 17.4 x 2.4	13	0.9
082-500-4	50' (15 m)	0.500 x 0.750 x 0.125	1/2 x 3/4 x 1/8	12.7 x 19.1 x 3.2	15	1.1
082-625-4	50' (15 m)	0.625 x 0.875 x 0.125	5/8 x 7/8 x 1/8	15.9 x 22.2 x 3.2	13	0.9
082-750-4	15' (4.5 m)	0.750 x 1.00 x 0.125	3/4 x 1 x 1/8	19.0 x 25.4 x 3.2	11	0.8
082-750-6	15' (4.5 m)	0.750 x 1.125 x 0.188	3/4 x 1 3/8 x 3/16	19.0 x 28.3 x 4.8	15	1
082-750-8	15' (4.5 m)	0.750 x 1.250 x 0.250	3/4 x 1 1/4 x 1/4	19.0 x 31.7 x 6.4	19	1.3
082-1000-6	15' (4.5 m)	1.00 x 1.375 x 0.188	1 x 1 3/8 x 3/16	25.4 x 34.9 x 4.8	11	0.8
082-1000-8	15' (4.5 m)	1.00 x 1.500 x 0.250	1 x 1 1/2 x 1/4	25.4 x 38.1 x 6.4	15	1





# International Filter Products

Revolutionary systems for your industry

## C-Flex® 082 TPE Tubing

### Ordering Guide



[1]	[2]
Inner Diameter [ID] Code	Wall Thickness Code
<ul style="list-style-type: none"> <li>• <b>031</b>: 0.031 inch or 1/32 inch</li> <li>• <b>063</b>: 0.063 inch or 1/16 inch</li> <li>• <b>125</b>: 0.125 inch or 1/8 inch</li> <li>• <b>188</b>: 0.188 inch or 3/16 inch</li> <li>• <b>250</b>: 0.250 inch or 1/4 inch</li> <li>• <b>313</b>: 0.313 inch or 5/16 inch</li> <li>• <b>375</b>: 0.375 inch or 3/8 inch</li> <li>• <b>500</b>: 0.500 inch or 1/2 inch</li> <li>• <b>625</b>: 0.625 inch or 5/8 inch</li> <li>• <b>750</b>: 0.750 inch or 3/4 inch</li> <li>• <b>1000</b>: 1.00 inch or 1 inch</li> </ul>	<ul style="list-style-type: none"> <li>• <b>1</b>: 0.031 inch or 1/32 inch</li> <li>• <b>2</b>: 0.063 inch or 1/16 inch</li> <li>• <b>3</b>: 0.094 inch or 3/32 inch</li> <li>• <b>4</b>: 0.125 inch or 1/8 inch</li> <li>• <b>6</b>: 0.188 inch or 3/16 inch</li> <li>• <b>8</b>: 0.250 inch or 1/4 inch</li> </ul>

### Example:

**082-125-2**

C-Flex 082 - Thermoplastic Elastomer Tubing, ID 0.125 in X OD 0.250 in X Wall thickness 0.062 in, Average Working Pressure 27 PSI at 66°F (19°C), 50 Ft per Coil

Part Number

Description

